




869757

## SDR Series Micrometer Adjustable Click Wrench, 30 - 150 ft-lb









### PRODUCT DETAILS

- Adjust torque value by rotating the grip
- Grip lock makes locking in torque value fast, easy, and secure
- Tool changes from one end of the scale to the other with the fewest number of turns
- Ball-bearing rock-over assembly assures smooth operation enhances repeatability and increases wrench service life
- Accuracy of +/- 4% of Indicated Value from 20% to 100% of rated capacity
- Meets or exceeds requirements of ASME B107.300-2010 and ISO 6789
- Error Proofing By Guidance design provides a strong audible and tactile impulse when the set torque is achieved
- Error Proofing By Design flattened case provides the mechanism with superior support resulting in a wrench that is easier to calibrate and one that holds calibration longer
- Flattened case prevents side loading during torque application or testing/calibration
- Knurled grip offers an ergonomic grip that remains comfortable over long periods of use
- Ratchet is built for durability
- Ratchet replacement is fast and easy when needed
- All tools up to 250 ft-lb capacity come with a rugged, custom-molded plastic case
- Includes FREE tabulated calibration certificate from our ISO 17025 certified calibration laboratory
- PLEASE NOTE: See below for manuals & details drawings; click the drop down menu, click on specific product PDF, click the download button



## PRODUCT ATTRIBUTES

Product: **869757**

<b>MODEL</b>	4SDR 150 MG	 lbf·ft	30-150 lbf·ft	 lbf·ft	1 lbf·ft
 lbf·in		 in·b			1/2 in
<b>A</b>	19.5 in	<b>B</b>	1.9 in	<b>C</b>	1.4 in
<b>D</b>	0.9 in	 lb	2.0 lb		