



874137


## BLT Bidirectional Preset Click-Type Torque Wrench, 960 - 4800 in-lb



### PRODUCT DETAILS

- SR Dovetail Head connects to over 100 SR Interchangeable Heads
- Error Proofing By Design: the SR Dovetail transmits the load at a right angle from the wrench to the head, providing exceptional strength and rigidity of the connection
- A pin lock on the dovetail assures positive head connection, yet permits head changeover in seconds
- CW +/- 4% Indicated Value Accuracy and CCW +/- 6% Indicated Value Accuracy from 20% to 100% of capacity, meeting or exceeding the requirements of ASME B107.300-2010 and ISO 6789
- we preset the tool to your requested torque value and we include a Certificate of Calibration from our ISO 17025 Accredited Lab
- Error Proofing By Behavior Modification: excellent tactile and audible pulse when the preset torque is achieved
- Error Proofing By Design: the flattened case prevents side-loading and ensures greater accuracy and durability
- Comfortable cushion grip plus light-weight for excellent ergonomics
- Preset and locked in with a special CART tool
- Torque can be set using any unit of measurement
- Can be ordered preset from the factory or you can set the torque with your own torque tester
- All of our tools provide torque measurements in the clockwise direction
- BLT preset click wrench measures torque in both clockwise and counterclockwise directions
- PLEASE NOTE: See below for manuals & details drawings; click the drop down menu, click on specific product PDF, click the download button

PRODUCT ATTRIBUTES

Product	MODEL	 N·m
<b>874137</b>	BLT 4800I	108.4-542 N·m