



Representative

**Catalog Number:** A1200 1T316SS  
**Product ID:** 7TAA005980R0105  
**UPC Number:** 61601310506  
**Status:** Active

Channel, 12 Gauge, 1-5/8 Inch x 1-5/8 Inch, Length 1 Foot, Type 316 Stainless Steel

### North American Specifications (UNSPSC)

UNSPSC	30101805 Stainless steel channels
IGCC	2578 Stainless steel channels
Brand Name	Superstrut
Type	Metal Channels
Special Features	Designed so that the maximum number of support and framing applications can be constructed with a minimum amount of labor and pieces.
Application	Used to mount, brace, support or connect structural loads in building construction such as pipe or electrical or data wire
Length	1 Foot
Width	1-5/8 Inch
Depth	1-5/8 Inch
Gauge	12 Gauge
Material Composition	Stainless Steel
Material Standard	Type 316

### European Specifications (ETIM)

ETIM	EC000386 Support/profile rail
Profile shape	U-profile
Model	Simple profile
Type of perforation	None
With tothing	N
Snap-off	N
Material	Steel
Material quality	Stainless steel
Colour	None

### Packaging

Outer Quantity	1
Outer Dimensions (inches)	12x1.63x1.63
Weight Uom	174 lbs. per 100

### Documents / Support Tools

Technical Data Sheet US	Available on Website
-------------------------	----------------------

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email:techsupport@tnb.com