



Representative

**Catalog Number:** A1200 20FT 7/8IN  
**Product ID:** 7TAA005920R0013  
**UPC Number:** 61601311486  
**Status:** Active

Channel, 12 Gauge, 1-5/8 Inch x 1-5/8 Inch, Length 20 Feet 7/8 Inches, Steel

### North American Specifications (UNSPSC)

UNSPSC	30101804 Steel channels
IGCC	2577 Steel channels
Brand Name	Superstrut
Type	Metal Channels
Special Features	Designed so that the maximum number of support and framing applications can be constructed with a minimum amount of labor and pieces.
Application	Support and framing applications
Length	20 Feet 7/8 Inches
Width	1-5/8 Inch
Depth	1-5/8 Inch
Gauge	12 Gauge
Material Composition	Steel
Finish	GoldGalv/Standard

### European Specifications (ETIM)

ETIM	EC000386 Support/profile rail
Profile shape	U-profile
Model	Simple profile
Type of perforation	None
With tothing	N
Snap-off	N
Material	Steel
Material quality	Other
Colour	None

### Packaging

Inner Quantity	1
Inner Dimensions (inches)	240.9x1.63x1.63
Outer Quantity	25
Outer Dimensions (inches)	240.9x10.25x6.8
Weight Uom	3854.8 lbs. per 100

### Documents / Support Tools

Technical Data Sheet US	Available on Website
-------------------------	----------------------

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: techsupport@tnb.com