



Representative

Catalog Number: A1200HS 1'6" T316SS
Product ID: 7TAA005980R0116
UPC Number: 61601310893
Status: Active

Channel, 12 Gauge, 1-5/8 Inch x 1-5/8 Inch, Length 15 Feet, Half Slotted Type 316 Stainless Steel with 9/16 Inch x 1-1/8 Inch Slots on 2 Inch Centers

North American Specifications (UNSPSC)

UNSPSC	30101805 Stainless steel channels
IGCC	2578 Stainless steel channels
Brand Name	Superstrut
Type	Metal Channels
Special Features	Designed so that the maximum number of support and framing applications can be constructed with a minimum amount of labor and pieces.
Application	Used to mount, brace, support or connect structural loads in building construction such as pipe or electrical or data wire
Length	15 Feet
Width	1-5/8 Inch
Depth	1-5/8 Inch
Gauge	12 Gauge
Slot Size	9/16 Inch
Material Composition	Stainless Steel
Material Standard	Type 316

European Specifications (ETIM)

ETIM	EC000386 Support/profile rail
Profile shape	U-profile
Model	Simple profile
Type of perforation	Back perforated
With toothing	N
Snap-off	N
Material	Steel
Material quality	Stainless steel
Colour	None

Packaging

Outer Quantity	1
Outer Dimensions (inches)	18x1.63x1.63
Weight Uom	262 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com