

Catalog Number: A1204 10HDG
Product ID: 7TAA005700R0024
UPC Number: 61601311955
Status: Active

Channel, 12 Gauge, 1-5/8 Inch x 1-5/8 Inch, Length 10 Feet, Hot-Dip Galvanized Steel, Two Sets of Channels Back to Back Combination

North American Specifications (UNSPSC)

UNSPSC	30101804 Steel channels
IGCC	2577 Steel channels
Brand Name	Superstrut
Type	Metal Channels
Special Features	Designed so that the maximum number of support and framing applications can be constructed with a minimum amount of labor and pieces.
Application	Support and framing applications
Length	10 Feet
Width	1-5/8 Inch
Depth	1-5/8 Inch
Gauge	12 Gauge
Material Composition	Steel
Finish	Hot-Dip Galvanized

European Specifications (ETIM)

ETIM	EC000386 Support/profile rail
Profile shape	U-profile
Model	Double profile
Type of perforation	None
With tothing	N
Snap-off	N
Material	Steel
Material quality	Other
Surface protection	Hot-dip galvanized
Colour	None

Packaging

Inner Quantity	10
Inner Dimensions (inches)	120x3.25x3.25
Outer Quantity	120
Outer Dimensions (inches)	120x16.25x12
Weight Uom	761.8 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com