



Representative

Catalog Number: A1400HSEG KIT
Product ID: 7TAA005920R0074
UPC Number: 61601311296
Status: Active

Channel. Half Slot, 9/16 inch X 1-1/8 Inch inch slots on 2 Inch centers. A Series, 14 Gauge, Depth 1-5/8 inches X Width 1-5/8 inches. 6 Foot Length. SilverGalv Finish. Will not form white rust when left outdoors. Will not chip, peel or crack. Superior corrosion resistant. Ends and punched holes are protected. Clean, paintable surface. 50 Pieces.

North American Specifications (UNSPSC)

UNSPSC	30101804 Steel channels
IGCC	2577 Steel channels
Brand Name	Superstrut
Type	Metal Channels
Special Features	Designed so that the maximum number of support and framing applications can be constructed with a minimum amount of labor and pieces.
Application	Used to mount, brace, support or connect structural loads in building construction such as pipe or electrical or data wire
Length	6 Feet
Width	1-5/8 Inch
Depth	1-5/8 Inch
Gauge	14 Gauge
Material Composition	Steel
Finish	Pre-Galvanized

European Specifications (ETIM)

ETIM	EC000386 Support/profile rail
Profile shape	U-profile
Model	Simple profile
Type of perforation	Back perforated
With tothing	N
Snap-off	N
Material	Steel
Material quality	Other
Colour	None

Packaging

Inner Quantity	1
Outer Quantity	50
Outer Dimensions (inches)	9.8x4.9x4.6
Weight Uom	0.73 lbs. Each

Documents / Support Tools

Technical Data Sheet US	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com