



Representative

Catalog Number: A1400HSGR KIT
Product ID: 7TAA005980R0193
UPC Number: 61601311570
Status: Active

Channel. Half Slot, 9/16 inch X 1-1/8 Inch inch slots on 2 Inch centers. A Series, 14 Gauge, Depth 1-5/8 inches X Width 1-5/8 inches. 6 inch Length. Green Urethane Powder Coated, resins are applied electrostatically to steel after fabrication. A Minimum of 1.5 mil thickness provides excellent resistance to chipping or peeling. 50 pieces

North American Specifications (UNSPSC)

UNSPSC	30101804 Steel channels
IGCC	2577 Steel channels
Brand Name	Superstrut
Type	Metal Channels
Special Features	Designed so that the maximum number of support and framing applications can be constructed with a minimum amount of labor and pieces.
Application	Used to mount, brace, support or connect structural loads in building construction such as pipe or electrical or data wire
Length	6 Inches
Width	1-5/8 Inch
Depth	1-5/8 Inch
Gauge	14 Gauge
Material Composition	Steel
Finish	Green Urethane Powder

European Specifications (ETIM)

ETIM	EC000386 Support/profile rail
Profile shape	U-profile
Model	Simple profile
Type of perforation	Back perforated
With tothing	N
Snap-off	N
Material	Steel
Material quality	Other
Colour	None

Packaging

Inner Quantity	1
Inner Dimensions (inches)	.5x1.63x1.63
Outer Quantity	50
Outer Dimensions (inches)	9.8x4.9x4.6
Weight Uom	73 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com