



Representative

Catalog Number: A215 AL
Product ID: 7TAA005900R0017
UPC Number: 61601312164
Status: Active

Aluminum Internal Splice Plate, 7.25 inch X 1.25 inch X 1/2 inch thick

North American Specifications (UNSPSC)

UNSPSC	31162307 Mounting plates
IGCC	2982 Mounting plates
Brand Name	Superstrut
Type	Fittings, Brackets & Hardware
Special Features	Excellent corrosion resistance
Application	For use in metal framing applications
Material	Aluminum
Number Of Holes	3
Width	1-1/4 Inch
Length	7-1/4 Inches
Plate Type	Splice

European Specifications (ETIM)

ETIM	EC000483 Coupler for support/profile rail
Suitable for	U-profile
Model	Exterior coupler
With screw accessories	N
Material	Aluminium

Packaging

Outer Quantity	25
Outer Dimensions (inches)	7.9x4.2x4.2
Weight Uom	19.5 lbs. per 100

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com