



Representative

**Catalog Number:** AB224 EG  
**Product ID:** 7TAA005290R0024  
**UPC Number:** 61601311758  
**Status:** Active

Angular Fitting. 22-1/2 Degree Bend. SilverGalv Finish. Will not form white rust when left outdoors. Will not chip, peel or crack. Superior corrosion resistant. Ends and punched holes are protected. Clean, paintable surface.

### North American Specifications (UNSPSC)

UNSPSC	31162502 Angle brackets
IGCC	3010 Angle brackets
Brand Name	Superstrut
Material	Steel
Width	1-5/8 Inches
Finish	SilverGalv/Electro-Galvanized
Color	Silver
Number Of Holes	4

### European Specifications (ETIM)

ETIM	EC000483 Coupler for support/profile rail
Suitable for	U-profile
Model	Angle
With screw accessories	N
Material	Steel
Surface protection	Galvanic/electrolytic zinc plated

### Packaging

Outer Quantity	25
Outer Dimensions (inches)	7.5x7.5x6.62
Weight Uom	72 lbs. per 100

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)