



Representative

**Catalog Number:** AB279 HDG  
**Product ID:** 7TAA005760R0055  
**UPC Number:** 61601311248  
**Status:** Active

90 Degree Angle Fitting, 5.375 inch tall X 3.875 inch wide narrowed down to 1.63 inch with 2 holes, other side is 1.875 inch wide with 3 holes, 1/4 inch thick, Hot dipped galvanized steel.

### North American Specifications (UNSPSC)

UNSPSC	31162502 Angle brackets
IGCC	3010 Angle brackets
Brand Name	Superstrut
Application	For use in metal framing applications
Material	Steel
Finish	Hot-Dip Galvanized
Number Of Holes	2

### European Specifications (ETIM)

ETIM	EC000483 Coupler for support/profile rail
Suitable for	U-profile
Model	Angle
With screw accessories	N
Material	Steel
Surface protection	Hot-dip galvanized

### Packaging

Outer Quantity	10
Outer Dimensions (inches)	1x1x1
Weight Uom	1 lbs. Each

### Documents / Support Tools

Technical Data Sheet Global	wsd-000088
-----------------------------	------------

For further technical assistance, please contact us...

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)