



Representative

Catalog Number: AB279SS316
Product ID: 7TAA005540R0038
UPC Number: 61601311253
Status: Active

90 Degree Angle Fitting, 316 Stainless Steel, 5.375 inch X 1.875 inch side with 3 holes, second side is 5.375 inch narrowing down to 1.63 inch over 3.875 inches with 2 holes. 1/4 inch thick.

North American Specifications (UNSPSC)

UNSPSC	31162502 Angle brackets
IGCC	3010 Angle brackets
Brand Name	Superstrut
Application	For use in metal framing applications
Material	Stainless Steel
Height	3.875 Inches
Width	1.875 Inches
Depth	5.375 Inches
Number Of Holes	5
Thickness	1/4 Inch

European Specifications (ETIM)

ETIM	EC000483 Coupler for support/profile rail
Suitable for	U-profile
Model	Angle
With screw accessories	N
Material	Steel
Material quality	Stainless steel

Packaging

Outer Quantity	10
Outer Dimensions (inches)	1x1x1
Weight Uom	1.47 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com