



Representative

Catalog Number: H1200 10GR
Product ID: 7TAA005490R0025
UPC Number: 61601309518
Status: Active

Channel, 12 Gauge, 1-5/8 Inch x 3-1/4 Inch, Length 10 Feet, Green Urethane Powder Coated Steel

North American Specifications (UNSPSC)

UNSPSC	30101804 Steel channels
IGCC	2577 Steel channels
Brand Name	Superstrut
Type	Metal Channels
Special Features	Designed so that the maximum number of support and framing applications can be constructed with a minimum amount of labor and pieces.
Application	Support and framing applications
Length	10 Feet
Width	1-5/8 Inch
Depth	3-1/4 Inches
Gauge	12 Gauge
Material Composition	Steel
Finish	Green Urethane Powder

European Specifications (ETIM)

ETIM	EC000386 Support/profile rail
Profile shape	U-profile
Model	Simple profile
Type of perforation	None
With toothing	N
Snap-off	N
Material	Steel
Material quality	Other
Colour	None

Packaging

Inner Quantity	10
Inner Dimensions (inches)	120x1.63x3.25
Outer Quantity	200
Outer Dimensions (inches)	120x10.2x6.7
Weight Uom	305 lbs. per 100

Documents / Support Tools

SDS US 1	sds-00046-tb2
Technical Data Sheet US	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com