



Representative

**Catalog Number:** H1200P 10GR  
**Product ID:** 7TAA005980R1013  
**UPC Number:** 61601310797  
**Status:** Active

Channel, 12 Gauge, 1-5/8 Inch x 3-1/4 Inch, Length 10 Feet, Punched Green Urethane Powder Coated Steel with 9/16 Inch Holes on 1-7/8 Inch Centers

### North American Specifications (UNSPSC)

UNSPSC	30101804 Steel channels
IGCC	2577 Steel channels
Brand Name	Superstrut
Type	Metal Channels
Special Features	Designed so that the maximum number of support and framing applications can be constructed with a minimum amount of labor and pieces.
Application	Support and framing applications
Length	10 Feet
Width	1-5/8 Inch
Depth	3-1/4 Inches
Gauge	12 Gauge
Slot Size	9/16 Inch
Material Composition	Steel
Finish	Urethane Powder
Color	Green

### European Specifications (ETIM)

ETIM	EC000386 Support/profile rail
Profile shape	U-profile
Model	Simple profile
Type of perforation	Back perforated
With tothing	N
Snap-off	N
Material	Steel
Material quality	Other
Colour	None

### Packaging

Inner Quantity	10
Inner Dimensions (inches)	120x1.63x3.25
Outer Quantity	200
Outer Dimensions (inches)	120x10.25x8.2
Weight Uom	293 lbs. per 100

### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email:techsupport@tnb.com