



Representative

**Catalog Number:** SP A1200HS 10B  
**Product ID:** 7TAA005980R1163  
**UPC Number:** 61601309272  
**Status:** Active

Channel, 12 Gauge, 1-5/8 Inch x 1-5/8 Inch, Length 10 Feet, Half Slotted Black Finish Steel with 9/16 Inch x 1-1/8 Inch Slots on 2 Inch Centers

### North American Specifications (UNSPSC)

UNSPSC	30101804 Steel channels
IGCC	2577 Steel channels
Brand Name	Superstrut
Type	Metal Channels
Special Features	Designed so that the maximum number of support and framing applications can be constructed with a minimum amount of labor and pieces.
Application	Support and framing applications
Length	10 Feet
Width	1-5/8 Inch
Depth	1-5/8 Inch
Gauge	12 Gauge
Material Composition	Steel
Finish	Black

### European Specifications (ETIM)

ETIM	EC000386 Support/profile rail
Profile shape	U-profile
Model	Simple profile
Type of perforation	Back perforated
With tothing	N
Snap-off	N
Material	Steel
Material quality	Other
Colour	None

### Packaging

Inner Quantity	10
Inner Dimensions (inches)	120x1.63x1.63
Outer Quantity	500
Outer Dimensions (inches)	120x10.2x9
Weight Uom	177 lbs. per 100

### Documents / Support Tools

SDS US 1	sds-00046-tb2
----------	---------------

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: techsupport@tnb.com