



Representative

Catalog Number: SP A1202 10SS
Product ID: 7TAA005570R0008
UPC Number: 61601309084
Status: Active

Channel, 12 Gauge, 1-5/8 Inch x 1-5/8 Inch, Length 10 Feet, Stainless Steel, Back to Back Combination

North American Specifications (UNSPSC)

UNSPSC	30101805 Stainless steel channels
IGCC	2578 Stainless steel channels
Brand Name	Superstrut
Type	Metal Channels
Special Features	Designed so that the maximum number of support and framing applications can be constructed with a minimum amount of labor and pieces.
Application	Used to mount, brace, support or connect structural loads in building construction such as pipe or electrical or data wire
Length	10 Feet
Width	1-5/8 Inch
Depth	1-5/8 Inch
Gauge	12 Gauge
Material Composition	Stainless Steel

European Specifications (ETIM)

ETIM	EC000386 Support/profile rail
Profile shape	U-profile
Model	Double profile
Type of perforation	None
With tothing	N
Snap-off	N
Material	Steel
Material quality	Stainless steel
Colour	None

Packaging

Inner Quantity	10
Inner Dimensions (inches)	120x1.63x3.26
Outer Quantity	250
Outer Dimensions (inches)	120x10.2x6.51
Weight Uom	1.9 lbs. Each

Documents / Support Tools

SDS US 1	sds-00046-tb2
----------	---------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com