



Representative

**Catalog Number:** ZA716 1-10  
**Product ID:** 7TAA005120R0059  
**UPC Number:** 61601312926  
**Status:** Active

Clamp, Cushioned, Tube Series, Outer Diameter Tubing Size 1 Inch, Steel

### North American Specifications (UNSPSC)

UNSPSC	31162905 Beam clamps
IGCC	3063 Beam clamps
Brand Name	Superstrut
Type	Pipe Straps, Pipe Clamps & Hangers (Series 700)
Special Features	Assembly includes steel clamp with bolt/locknut and cushion.
Application	To secure pipes, tubes and hoses for fluid conductors.
Material	Steel
Finish	GoldGalv/Standard
Length	2.606 Inches
Width	1-1/4 Inch
Maximum Clamp Diameter	1 Inch
Gauge	14 Gauge

### European Specifications (ETIM)

ETIM	EC002470 Mounting clamp for cable protection tubes
Material	Steel
Rotatable	N

### Packaging

Outer Quantity	10
Outer Dimensions (inches)	8.4x6.9x5.9
Weight Uom	9.5 lbs. per 100

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)