



Representative

Catalog Number: ZA716 1/2-10
Product ID: 7TAA005120R0057
UPC Number: 61601312924
Status: Active

Clamp, Cushioned, Tube Series, Outer Diameter Tubing Size 1/2 Inch, Steel

North American Specifications (UNSPSC)

UNSPSC	31162905 Beam clamps
IGCC	3063 Beam clamps
Brand Name	Superstrut
Type	Pipe Straps, Pipe Clamps & Hangers (Series 700)
Special Features	Assembly includes steel clamp with bolt/locknut and cushion.
Application	To secure pipes, tubes and hoses for fluid conductors.
Material	Steel
Finish	GoldGalv/Standard
Length	2.089 Inches
Width	1-1/4 Inch
Maximum Clamp Diameter	1/2 Inch
Gauge	14 Gauge

European Specifications (ETIM)

ETIM	EC002470 Mounting clamp for cable protection tubes
Material	Steel
Rotatable	N

Packaging

Outer Quantity	10
Outer Dimensions (inches)	8.3x3.7x5.8
Weight Uom	14 lbs. per 100

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com