



CODE/ADDENDA _____ APPROVED _____
 RELEASED FOR PRODUCTION
 Q.C. _____ DATE _____



FIND NO.	NPT SIZE
F1	2
F2	1
F3	1/2
F4	1/4
F5	1-1/2

SYM	DATE	BY	REVISION	APP	NOTES	SPECIFICATIONS	200ARV200 :3000		
A		EGB				O.D.: 30 LGTH: 72 MAWP: 200 PSI @ 400° F RT MDMT- F@ PSI EXMT: X-RAY: CRN# --	VERTICAL AIR RECIEVER 200 GALLON		
B		JC		TA	GAL: 200 SA: 51 ft ² WT: 450 # CU.FT: 27 CORR ALW: SH HD CODE: ASME / NB PER DATE OF DWG/LAST REV				SCALE: NONE
C		JC		JC					WELD DETAILS M-1932 STD. TOLERANCES (UNLESS OTHERWISE NOTED) M-2461