



## Limit Switch Ready Winch Options

Model	Description
NOTE: Limit switch winch option requires purchase of limit switch and headache ball (sold separately)	
<b>For 5PF5, 5PA5, 5PA10, 5PT5, 5PT10 , 5PT20 Series Cranes (sold separately)</b>	
E2L (5PA5, 5PA10)	4WP2V electric winch—115/1/60 VAC with 6 ft pendant control—enamel
E2LX (5PA5, 5PA10)	4WP2VEGRA electric winch—115/1/60 VAC with 6 ft pendant control—epoxy gray
E4L	4777 electric winch—115/1/60 VAC with 6 ft pendant control—enamel
E4LX	4777EGRA electric winch—115/1/60 VAC with 6 ft pendant control—epoxy gray
E4DCL	4777DC electric winch—12 volt DC with 10 ft pendant control—enamel
E4DCLX	4777DCEGRA electric winch—12 volt DC with 10 ft pendant control—epoxy gray
<b>For 5FT20 Series Crane Only (sold separately)</b>	
E2L	4WP2 electric winch—115/1/60 VAC with 6 ft pendant control—enamel
E2LX	4WP2EGRA electric winch—115/1/60 VAC with 6 ft pendant control—epoxy gray
E4L	4771 electric winch—115/1/60 VAC with 6 ft pendant control—enamel finish
E4LX	4771EGRA electric winch—115/1/60 VAC with 6 ft pendant control—gray-epoxy finish
E4DCL	E4DCL 4771DC electric winch—12 volt DC with 10 ft pendant control—enamel finish
E4DCLX	4771DCEGRA electric winch—12 volt DC with 10 ft pendant control—gray-epoxy finish
<b>For 5PT30, 5FT25, 5FT40 Series Crane Only (sold separately)</b>	
E2L	3WG4B electric winch—115/1/160 VAC with 6 ft pendant control—enamel finish
E2LX	3WG4BEGRA electric winch—115/1/160 VAC with 6 ft pendant control—epoxy-gray finish
E2TL	3WG4BMT electric winch—115/1/160 VAC with 6 ft pendant control—enamel finish (Unavailable for use with 5FT40)
E2TLX	3WG4MTX electric winch—115/1/160 VAC with 6 ft pendant control—epoxy-gray finish

## Drill Drive Kit

Model	Description
ED330-DW11	120 VAC, 11-amp, 330 rpm drill motor to power drive the hand winch. Only available for cranes configured with the M2 winch option. Includes 1-1/8" hex drive socket
ED300-DW06	Cordless drill kit, 60 V brushless motor, 300 rpm drill motor to power drive the M2 hand winch option. Includes 1-1/8" hex drive socket
ED400-DW09	Heavy-duty cordless drill kit, 60 V brushless motor, 400 rpm drill motor to power drive the M2 hand winch option. Includes 1-1/8" hex drive socket

## Headache Ball

Model	Description
HB10-12-25	Red enamel painted 10 lb fits 1/8" to 1/4" rope
HB10-25-38	Red enamel painted 10 lb fits 1/4" to 3/8" rope
HB10S-12-25	Stainless-steel 10 lb fits 1/8" to 1/4" rope
HB10S-25-38	Stainless-steel 10 lb fits 1/4" to 3/8" rope
HB10S-44-50	Stainless-steel 10 lb fits 7/16" to 1/2" rope

## Base Extension

Model	Description
5BE5-15	15" (38 cm) base extension available on 5PF5, 5PT5, 5PT10, and 5PT20 with powder-coat, galvanized, 304 & 316 stainless-steel, and epoxy finishes
5BE10-15	
5BE20-15	

## Workmate

Model	Description
5BH5	Portable hitch-mounted crane base is compatible with the 5PF5, 5PT5, and 5PA5 davit models.