



Actual

Catalog Number: 035-72775-10
Product ID: 7TBD012360R0001
UPC Number: 78621086869
EAN Number: 05415022435269
Status: A

3/4 Inch Straight Die Cast Zinc Liquidtight Strain Relief Cord Connector, Cord Range 0.500 to 0.625

- Extended range with superior strain relief

North American Specifications (UNSPSC)

| | |
|------------------|--|
| UNSPSC | 39121420 Liquid tight connectors |
| IGCC | 4585 Liquid tight connectors |
| Type | Strain Relief Cord Connectors-Straight |
| Special Features | Throat Inner Diameter is Nylon Coated for Ease of Wire Pull |
| Application | Provide Means for Passing a Cord Cable, Armored or Unarmored, Into an Enclosure, Through a Bulk-head or Into a Rigid Conduit |
| Size | 3/4 Inch |
| Material | Zinc Die Cast |

European Specifications (ETIM)

| | |
|---|--|
| ETIM | EC001180 Screw connection for protective metallic hose |
| Nominal size in inch | 3/4 inch |
| Model | Straight |
| Revolving thread | N |
| Construction type | External thread |
| Connection type screw connection to housing | Thread |
| Thread type | NPT |
| Thread connection size | None |
| Material housing | Zinc die-cast |

Packaging

| | |
|---------------------------|-------------------|
| Inner Quantity | 10 |
| Inner Dimensions (inches) | 4x4x3 |
| Outer Quantity | 100 |
| Outer Dimensions (inches) | 24x11x4.2 |
| Weight Uom | 19.5 lbs. per 100 |