



Actual

Catalog Number: 13-264
Product ID: 7TAA008010R0062
UPC Number: 78378613264
Status: A

Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (220 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, Length of 363.22mm (14.3 Inches), Width of 4.673mm (0.184 Inches), Thickness of 1.24mm (0.049 Inches), Tensile Strength Rating of 220 Newtons (50 Pounds)

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	Standard
Application	For Temperatures up to 105 Degrees Celsius (220 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications
Standard	UL E49405
Width	0.184 in ; 4.673 mm
Length	14.3 in ; 363.22 mm
Thickness	0.049 in ; 1.24 mm
Bundle Diameter	4 in ; 101.6 mm
Material	Polyamide/Nylon 6.6
Color	Black
Lock Mechanism	Double Locking Head
Tensile Strength	50 pounds ; 220 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	4.63
Length belt/tape/tie	363.22
Tie thickness	1.24
Min. holding force	220
Operating temperature	-40-+85
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide PA
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N
UL approval	N

Packaging

Inner Quantity	50
Inner Dimensions (inches)	19x5x1.5
Outer Quantity	500
Outer Dimensions (inches)	15.5x6x5.6
Weight Uom	6.88 lbs. per 1000

