



Representative

Catalog Number: 1948
Product ID: 7TAD013130R0004
UPC Number: 78621001948
Status: A

2-1/2 Inch Chase Nipple, Malleable Iron, Nylon Insulated for Use with Rigid/IMC Conduit

North American Specifications (UNSPSC)

UNSPSC	39131718 Electrical conduit nipple
IGCC	5753 Electrical conduit nipple
Type	Chase Conduit Nipple
Application	To Effectively Bush Factory or Field-Punched, Cut, or Drilled Holes In Metal Boxes or Enclosures. To Couple Boxes Back-to-Back
Standard	UL E23018, CSA
Material	Malleable Iron
Trade Size	2-1/2 in

European Specifications (ETIM)

ETIM	EC001469 Protective hose adapter
Thread size outer thread metric	63
Material housing	Other
Material quality	Other
Surface protection	Untreated
Model	Straight

Packaging

Inner Quantity	5
Inner Dimensions (inches)	6.3x4.3x5.3
Outer Quantity	20
Outer Dimensions (inches)	10.6x8.6x9
Weight Uom	63 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001846
--------------------------------	------------

Header

3D Model	Available on Website
----------	----------------------