



Actual



Representative

**Catalog Number:** 2559  
**Product ID:** 7TBD105240R0018  
**UPC Number:** 78621002559  
**EAN Number:** 05414363101659  
**Status:** A

Liquidtight Strain Relief Cord Connector, 1-1/4 Inch, Straight, Cord Range 1.065 to 1.205 Inch, Die Cast Zinc

- Meets Coast Guard CG293

### North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Strain Relief Cord Connectors-Straight
Special Features	Meets Coast Guard CG293
Application	Suitable for Use In Hazardous Locations Where General Purpose Equipment is Specifically Permitted by NEC 501-4(B).
Standard	UL E13938, CSA
Size	1-1/4 Inch
Conductor Range	1.065 to 1.205 Inch
Material	Zinc Die Cast
Color	Metallic
Temperature Rating	105 C

### European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1 1/4 inch
Thread length	20.63mm
Suitable for cable diameter	27.05-30.61mm
Material	Metal
Material quality	Other
Colour	Natural colour
Model	Straight
Strain relief	Y
Operating temperature	0-+105°C

### Packaging

Inner Quantity	5
Inner Dimensions (inches)	6x4.5x3
Outer Quantity	50
Outer Dimensions (inches)	24.5x13x4
Weight Uom	56.81 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000046
Catalog Page	Available on Website
Support/Tools	Available on Website

### Header

3D Model	Available on Website
----------	----------------------

