



Actual



Representative

Catalog Number: 2565
Product ID: 7TBD105240R0021
UPC Number: 78621002565
EAN Number: 05414363134688
Status: A

Liquidtight Strain Relief Cord Connector, 1-1/2 Inch, Straight, Cord Range 1.375 to 1.625 Inch, Malleable Iron

- Meets Coast Guard CG293

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Strain Relief Cord Connectors-Straight
Special Features	Meets Coast Guard CG293
Application	Suitable for Use In Hazardous Locations Where General Purpose Equipment is Specifically Permitted by NEC 501-4(B).
Standard	UL E13938, CSA
Size	1-1/2 Inch
Conductor Range	1.375 to 1.625 Inch
Material	Malleable Iron
Color	Metallic
Temperature Rating	105 C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1 1/2 inch
Thread length	20.63mm
Suitable for cable diameter	34.92-41.28mm
Material	Metal
Material quality	Other
Colour	Natural colour
Model	Straight
Strain relief	Y
Operating temperature	0-+105°C

Packaging

Outer Quantity	5
Outer Dimensions (inches)	7.8x7x4.1
Weight Uom	95.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000046
Catalog Page	Available on Website
Support/Tools	Available on Website

Header

3D Model	Available on Website
----------	----------------------