



Actual



Representative

Catalog Number: 2633
Product ID: 7TAD105160R0002
UPC Number: 78621002633
EAN Number: 05414363140078
Status: A

Chase Liquidtight Steel Cord Connector, Straight, 1/2 Inch, Cord Range 0.375 to 0.500 Inch

- Meets Coast Guard CG293

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Chase Cord Connectors-Straight
Application	Suitable for use in hazardous locations in Class I, Div. 2; Class II, Div 1 & 2; Class III, Div 1 & 2, where general purpose equipment is specifically permitted by NEC 500-2(a).
Standard	UL E13938, CSA
Size	1/2 Inch
Material	Steel
Temperature Rating	105 C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1/2 inch
Suitable for cable diameter	9.525-12.7mm
Material	Other
Material quality	Steel
Colour	Natural colour
Model	Straight

Packaging

Inner Quantity	25
Inner Dimensions (inches)	6x4.5x3
Outer Quantity	50
Outer Dimensions (inches)	8.9x5.3x6.9
Weight Uom	19.06 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000049
Catalog Page	Available on Website
Support/Tools	Available on Website

Header

3D Model	Available on Website
----------	----------------------