



Actual

**Catalog Number:** 265  
**Product ID:** 7TAA106060R0004  
**UPC Number:** 78621000265  
**EAN Number:** 05415022240344  
**Status:** A

Squeeze Connector, 45 Degree Bend, Trade Size 3/8 Inch, Knockout Size 1/2 Inch, Cable Range 0.406 to 0.656 Inch, Steel

#### North American Specifications (UNSPSC)

UNSPSC	39121419 Flex connectors
IGCC	4573 Flex connectors
Type	Armored Cable/Flexible Metal Conduit Fittings
Special Features	Fast and Easy Installation, Simply Loosen Screws Partway to Lift off Cap
Application	For Use with Armored Cable and Flexible Metal Conduit
Standard	UL E23018, CSA 2884
Size	3/8 Inch
Conductor Range	0.406 to 0.656 Inch
Material	Steel
Finish	Zinc Plated
Color	Metallic
Insulation	No

#### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	3/8 inch
Model	45°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Steel
Thread length	28.58mm
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

#### Packaging

Inner Quantity	25
Inner Dimensions (inches)	6x4.5x3
Outer Quantity	100
Outer Dimensions (inches)	9.6x9x7
Weight Uom	11.5 lbs. per 100

#### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------