



Actual



Actual

**Catalog Number:** 277  
**Product ID:** 7TAA106070R0027  
**UPC Number:** 78621000277  
**Status:** A

Squeeze Connector, Straight, Trade Size 3 Inch, Knockout Size 3 Inch, Cable Range 3.312 to 3.563 Inch, Malleable Iron

### North American Specifications (UNSPSC)

UNSPSC	39121419 Flex connectors
IGCC	4573 Flex connectors
Type	Armored Cable/Flexible Metal Conduit Fittings
Special Features	T&B Squeeze Connectors Will Fit Every Size of Armored Cable, Leaded Cable and Flexible Conduit
Application	For Use with Armored Cable and Flexible Metal Conduit
Standard	UL E23018, CSA 2884
Size	3 Inch
Conductor Range	3.312 to 3.563 Inch
Material	Malleable Iron
Finish	Zinc Plated
Color	Metallic
Insulation	No

### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	3 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Other
Thread length	19.05mm
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

### Packaging

Inner Quantity	1
Inner Dimensions (inches)	5x4.5x3
Outer Quantity	5
Outer Dimensions (inches)	16.4x5.1x5.9
Weight Uom	195 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website