



Actual



Representative

**Catalog Number:** 2930  
**Product ID:** 7TBD105180R0000  
**UPC Number:** 78621002930  
**EAN Number:** 05414363101765  
**Status:** A

Liquidtight Strain Relief Connector, 3/4 Inch, Straight, Cord Range 0.125 to 0.375 Inch, Throat Diameter 13/16 Inch, Steel Body, Glandnut, and Grip, Rubber Bushing

- Reduced overall size, fits into tighter spaces.
- Gland nut designed to restrict cable bending.
- Suitable for Ordinary, Wet or Dry locations.
- Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).

**North American Specifications (UNSPSC)**

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Cord Connectors-Straight
Special Features	Extended Range with Superior Strain Relief
Application	Provide a Means for Passing a Cord Cable Into an Enclosure Through a Bulkhead
Standard	UL E13938, CSA 52391
Size	3/4 Inch
Conductor Range	0.125 to 0.375 Inch
Material	Steel
Color	Metallic
Environmental Conditions	Ordinary, Wet, or Dry Locations

**European Specifications (ETIM)**

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	3/4 inch
Thread length	19.05mm
Suitable for cable diameter	3.175-9.525mm
Material	Metal
Material quality	Steel
Colour	Natural colour
Model	Straight
Strain relief	Y

**Packaging**

Inner Quantity	10
Inner Dimensions (inches)	4x4x3
Outer Quantity	100
Outer Dimensions (inches)	21.9x9.1x4.19
Weight Uom	19.63 lbs. per 100

**Documents / Support Tools**

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

**Header**

3D Model	Available on Website
----------	----------------------

