



Representative

Catalog Number: 320
Product ID: 7TAA106040R0013
UPC Number: 78620992295
Status: A

Metal-Clad and Armored Cable Fitting, Straight, Trade Size 4 Inch, Knockout Size 4 Inch, Cable Range 4.120 to 4.560 Inch, Malleable Iron with Zinc Plating

- For use with Armored Cable and Flexible Metal Conduit

North American Specifications (UNSPSC)

UNSPSC	39121419 Flex connectors
IGCC	4573 Flex connectors
Type	Armored Cable/Flexible Metal Conduit Fittings
Special Features	Easy to Install with Double Grip Saddle, Connectors are Completely Salvageable
Application	To Connect and Effectively Bond Metal-Clad Cables, Armored Cable, and Flexible Metal Conduit to a Box or Enclosure
Standard	UL E23018
Size	4 Inch
Conductor Range	4.120 to 4.560 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated
Color	Metallic
Insulation	No

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	4 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Other
Surface protection	Zinc coated

Packaging

Outer Quantity	1
Outer Dimensions (inches)	6.75x5.62x4.87
Weight Uom	4.61 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

Header

3D Model	Available on Website
----------	----------------------