



Actual



Representative

Catalog Number: 3215
Product ID: 7TAD013590R0005
UPC Number: 78621003215
Status: A

One Piece Non Metallic Knockout Bushing, Thermoplastic, Knockout Size 2.469 for Use with Rigid/IMC Conduit

North American Specifications (UNSPSC)

UNSPSC	39121312 Electrical bushing
IGCC	4442 Electrical bushing
Type	Knockout Bushings & Plugs
Application	To Bush Knockout Openings In Metal Boxes or Enclosures
Standard	CSA, UL E3803
Size	2.469 Inch
Material	Polycarbonate
Color	Black

European Specifications (ETIM)

ETIM	EC001181 Sealing ring
Model	Other
Thickness	0.520mm
Material	Plastic
Fitting for thread size NPT	2.469

Packaging

Inner Quantity	25
Inner Dimensions (inches)	6x5x4
Outer Quantity	250
Outer Dimensions (inches)	26.25x13.25x5.25
Weight Uom	12.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

Header

3D Model	Available on Website
----------	----------------------