



Actual



Representative

**Catalog Number:** 4962  
**Product ID:** 7TBD105180R0005  
**UPC Number:** 78621004962  
**EAN Number:** 05414363190622  
**Status:** A

Liquidtight Strain Relief Connector, 1/2 Inch, 90 Degree Bend, Cord Range 0.500 to 0.750 Inch, Throat Diameter 19/32 Inch, Malleable Iron Body, Steel Gland, Plastic Grip, Santropene Bushing

- Reduced overall size, fits into tighter spaces.
- Gland nut designed to restrict cable bending.
- Suitable for Ordinary, Wet or Dry locations.
- Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).

### North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Cord Connectors-90 Degree
Special Features	Extended Range with Superior Strain Relief
Application	Provide a Means for Passing a Cord Cable Into an Enclosure Through a Bulkhead
Standard	UL E13938, CSA 52391
Size	1/2 Inch
Conductor Range	0.500 to 0.750 Inch
Material	Malleable Iron
Color	Metallic
Environmental Conditions	Ordinary, Wet, or Dry Locations

### European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1/2 inch
Suitable for cable diameter	12.7-19.05mm
Material	Metal
Material quality	Other
Colour	Natural colour
Model	90°-elbow

### Packaging

Inner Quantity	10
Inner Dimensions (inches)	5.2x3.2x4.6
Outer Quantity	50
Outer Dimensions (inches)	23.9x5.6x4
Weight Uom	29 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website

### Header

3D Model	Available on Website
----------	----------------------

