

**Catalog Number:** 52-W/OBC  
**Product ID:** 7TAA001490R0004  
**UPC Number:** 78172002240  
**Status:** Active

Gangable Switch Box, 12.5 Cubic Inches, 3 Inches Long x 2 Inches Wide x 2-1/2 Inches Deep, 1/2 Inch Knockouts, Galvanized Steel, Two Nail Holes in Sides, Furnished with Plaster Ears, without Bar Code, For use with Conduit

**North American Specifications (UNSPSC)**

UNSPSC	39121306 Switch box
IGCC	4430 Switch box
Brand Name	Steel City
Type	Switch Boxes
Application	For use with conduit
Material	Steel
Size	3 Inches Height x 2 Inches Width x 2-1/2 inches depth
Color	Silver
Cubic Capacity	12.5 Cubic Inches
Knockouts	Yes
Number Of Outlet	1

**European Specifications (ETIM)**

ETIM	EC000080 Surface mounted housing for flush mounted switching device
Assembly arrangement	Surface mounted housing
Mounting direction	Vertical
Material	Metal
Colour	Silver
Transparent	N
Width of device	50.8mm

**Packaging**

Outer Quantity	50
Outer Dimensions (inches)	20.81x8.62x7
Weight Uom	41.5 lbs. per 100

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com