



Representative

Catalog Number: 5229
Product ID: 7TAD012470R0004
UPC Number: 78621005229
EAN Number: 05414363099901
Status: A

Non-insulated, Straight, Steel, 1/4 Inch, Liquidtight Fitting

- Ability to install quickly with low torque effort
- To positively bond conduit to box or enclosure.

North American Specifications (UNSPSC)

| | |
|-------------|---|
| UNSPSC | 39121420 Liquid tight connectors |
| IGCC | 4585 Liquid tight connectors |
| Type | Connectors-Straight |
| Application | Used where flexible metal raceway is installed in outdoor or indoor locations where exposed to continuous or intermittent moisture. |
| Size | 1/4 Inch |
| Material | Steel |
| Finish | Electro Zinc Plated/Chromate Coating |

European Specifications (ETIM)

| | |
|---|--|
| ETIM | EC001180 Screw connection for protective metallic hose |
| Nominal size in inch | 1/4 inch |
| Model | Straight |
| Revolving thread | N |
| Construction type | External thread |
| Connection type screw connection to housing | Thread |
| Thread type | NPT |
| Thread connection size | Other |
| One-piece | N |
| Material housing | Steel |
| Thread length | 11.90mm |
| Total length | 34.92mm |
| Approved in combination with protective conduit CSA | N |
| Approved in combination with protective conduit UL | N |

Packaging

| | |
|---------------------------|------------------|
| Inner Quantity | 25 |
| Inner Dimensions (inches) | 3.5x3x3 |
| Outer Quantity | 100 |
| Outer Dimensions (inches) | 7.7x6.7x3.5 |
| Weight Uom | 7.5 lbs. per 100 |

Documents / Support Tools

| | |
|--------------------------------|-------------|
| Technical Drawing / Data Sheet | TDS000122 |
| Instruction Sheet | TA00210-TB2 |

Header

| | |
|----------|----------------------|
| 3D Model | Available on Website |
|----------|----------------------|

