



Actual



Family

Catalog Number: 5231-PT
Product ID: 7TAD012100R0043
UPC Number: 78620967404
Status: A

3/8 Inch Straight Zinc Plated Steel Liquidtight Push-in Connector, Non-insulated

- High performance and pull-out strength
- Installs up to 3 times faster
- No disassembly required

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Connectors-Straight
Special Features	Innovative Labor-Saving Design, Simple Push-In Connection
Application	For Liquid and Dust-Tight Connections Between Flexible Jacketed Metallic Conduit and a Box or an Enclosure
Standard	UL E23018, CSA
Size	3/8 Inch
Material	Steel
Finish	Zinc Plating

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	3/8 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Plug-in connection
Thread type	NPT
Thread connection size	Other
One-piece	Y
Material housing	Steel
Surface protection	Zinc coated
Operating temperature	0-+105°C

Packaging

Inner Quantity	25
Inner Dimensions (inches)	6x4.5x4
Outer Quantity	100
Outer Dimensions (inches)	9.56x8.63x6.31
Weight Uom	12.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000121
Instruction Sheet	TA04752-TB2
Support/Tools	Available on Website
Catalog US	Available on Website

