



Actual



Family

**Catalog Number:** 5234-PT  
**Product ID:** 7TAD012100R0034  
**UPC Number:** 78620967410  
**Status:** Active

1 Inch Straight Zinc Plated Steel Liquidtight Push-in Connector, Non-insulated

- High performance and pull-out strength
- Installs up to 3 times faster
- No disassembly required

### North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Brand Name	T&B
Type	Connectors-Straight
Special Features	Innovative Labor-Saving Design, Simple Push-In Connection
Application	For Liquid and Dust-Tight Connections Between Flexible Jacketed Metallic Conduit and a Box or an Enclosure
Standard	UL E23018, CSA
Size	1 Inch
Material	Steel
Finish	Zinc Plating

### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Plug-in connection
Thread type	NPT
Thread connection size	Other
One-piece	Y
Material housing	Steel
Surface protection	Zinc coated
Operating temperature	0-+105°C

### Packaging

Inner Quantity	10
Inner Dimensions (inches)	8x5x4
Outer Quantity	50
Outer Dimensions (inches)	20.81x5.18x8.12
Weight Uom	37.5 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000121
Technical Drawing / Data Sheet Canada	Available on Website
Instruction Sheet	TA04752-TB2
Catalog US	Available on Website

