



Representative

**Catalog Number:** 5234GR  
**Product ID:** 7TAD012310R0005  
**UPC Number:** 78621089985  
**Status:** A

1 Inch Steel External Bonding Liquidtight Connector, Steel, Grounded, Non-insulated

- Ability to install quickly with low torque effort

### North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Grounding Connectors-Straight
Application	To positively bond conduit to box or enclosure
Standard	UL E3060, CSA
Size	1 Inch
Material	Steel
Finish	Electro Zinc Plated/Chromate Coating

### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Steel
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

### Packaging

Inner Quantity	10
Inner Dimensions (inches)	8x5x4
Outer Quantity	50
Outer Dimensions (inches)	20.81x5.18x8.12
Weight Uom	39.5 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000120
Support/Tools	Available on Website
Catalog US	Available on Website

### Header

3D Model	Available on Website
----------	----------------------