



Actual



Representative

Catalog Number: 5343-HT
Product ID: 7TAD012420R0069
UPC Number: 78621091031
Status: A

3/4 Inch 45 Degree Malleable Iron Insulated Liquidtight High Temperature Connector

- Sure-Tight gland deflects water away from connector and prevents "pooling" of moisture.
- Double beveled sealing ring designed with 5 unique sealing mechanisms and cannot be installed backwards
- Safe Edge ground cone provides superior bonding, stronger pullout, easy threading and conductor protection.
- Double plating for superior corrosion protection
- Heat Curled Insulator molded inside body provides excellent wire protection and easier glide of conductors through and into the fitting.

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Connectors-45 Degree
Size	3/4 Inch
Material	Malleable Iron
Finish	Zinc Plating/Clear Chromate

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	3/4 inch
Model	45°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Steel
Surface protection	Zinc coated
Thread length	14.28mm
Approved in combination with protective conduit CSA	N
Approved in combination with protective conduit UL	N
Operating temperature	0-+150°C

Packaging

Inner Quantity	10
Inner Dimensions (inches)	6.25x4.75x3.25
Outer Quantity	50
Outer Dimensions (inches)	21.62x5.12x6.62
Weight Uom	43.75 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000123
Catalog Page	Available on Website
Instruction Sheet	TA02544-TB2

Support/Tools

Available on Website

Catalog US

Available on Website

Header

3D Model

Available on Website