



Actual

**Catalog Number:** 5343-SG  
**Product ID:** 7TAD012140R0007  
**UPC Number:** 78620992789  
**Status:** Active

3/4 Inch 45 Degree Malleable Iron Insulated Connector With Sealing Gasket

**North American Specifications (UNSPSC)**

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Brand Name	T&B
Type	Liquidtight Insulated Connector
Size	3/4 Inch
Connection	45 Degree
Material	Iron

**European Specifications (ETIM)**

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	3/4 inch
Model	45°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Other

**Packaging**

Inner Quantity	10
Inner Dimensions (inches)	6.25x4.75x4.25
Outer Quantity	50
Outer Dimensions (inches)	21.62x5.12x6.62
Weight Uom	40.4 lbs. per 100