



Actual



Representative

**Catalog Number:** 5344-HT  
**Product ID:** 7TAD012420R0071  
**UPC Number:** 78621091032  
**Status:** A

1 Inch 45 Degree Malleable Iron Insulated Liquidtight High Temperature Connector

- Sure-Tight gland deflects water away from connector and prevents "pooling" of moisture.
- Double beveled sealing ring designed with 5 unique sealing mechanisms and cannot be installed backwards
- Safe Edge ground cone provides superior bonding, stronger pullout, easy threading and conductor protection.
- Double plating for superior corrosion protection
- Heat Curled Insulator molded inside body provides excellent wire protection and easier glide of conductors through and into the fitting.

**North American Specifications (UNSPSC)**

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Connectors-45 Degree
Size	1 Inch
Material	Malleable Iron
Finish	Zinc Plating/Clear Chromate

**European Specifications (ETIM)**

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 inch
Model	45°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Steel
Surface protection	Zinc coated
Thread length	19.05mm
Approved in combination with protective conduit CSA	N
Approved in combination with protective conduit UL	N
Operating temperature	0-+150°C

**Packaging**

Inner Quantity	5
Inner Dimensions (inches)	6.25x4.75x3.25
Outer Quantity	25
Outer Dimensions (inches)	21.62x5.12x6.62
Weight Uom	56.88 lbs. per 100

**Documents / Support Tools**

Technical Drawing / Data Sheet	TDS000123
Instruction Sheet	TA02544-TB2
Support/Tools	Available on Website



Catalog US

Available on Website

**Header**

3D Model

Available on Website