



Representative

**Catalog Number:** 5347GR  
**Product ID:** 7TAD012310R0032  
**UPC Number:** 78621089631  
**EAN Number:** 05415022258929  
**Status:** A

2 Inch 45 Degree Malleable Iron External Bonding Liquidtight Insulated Connector

- Ability to install quickly with low torque effort

**North American Specifications (UNSPSC)**

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Grounding Connectors-45 degree
Application	To positively bond conduit to box or enclosure
Standard	UL E3060, CSA
Size	2 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated/Chromate Coating

**European Specifications (ETIM)**

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	2 inch
Model	45°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Other

**Packaging**

Inner Quantity	1
Inner Dimensions (inches)	6x4x4
Outer Quantity	5
Outer Dimensions (inches)	21.6x5.3x7.3
Weight Uom	256 lbs. per 100

**Documents / Support Tools**

Technical Drawing / Data Sheet	TDS000120
Support/Tools	Available on Website
Catalog US	Available on Website

**Header**

3D Model	Available on Website
----------	----------------------