



Actual



Representative

**Catalog Number:** 5357-HT  
**Product ID:** 7TAD012420R0100  
**UPC Number:** 78621091064  
**EAN Number:** 05415022257304  
**Status:** A

2 Inch 90 Degree Malleable Iron Insulated Liquidtight High Temperature Connector

- Sure-Tight gland deflects water away from connector and prevents "pooling" of moisture.
- Double beveled sealing ring designed with 5 unique sealing mechanisms and cannot be installed backwards
- Safe Edge ground cone provides superior bonding, stronger pullout, easy threading and conductor protection.
- Double plating for superior corrosion protection
- Heat Curled Insulator molded inside body provides excellent wire protection and easier glide of conductors through and into the fitting.

### North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Connectors-90 Degree
Size	2 Inch
Material	Malleable Iron
Finish	Zinc Plating/Clear Chromate

### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	2 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Other
Surface protection	Zinc coated
Thread length	22.22mm
Approved in combination with protective conduit CSA	N
Approved in combination with protective conduit UL	N
Operating temperature	0-+150°C

### Packaging

Inner Quantity	1
Inner Dimensions (inches)	6x4.5x3
Outer Quantity	5
Outer Dimensions (inches)	21.62x5.12x6.62
Weight Uom	2.8 lbs. Each

### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000123
Catalog Page	Available on Website

Instruction Sheet

TA02544-TB2

Support/Tools

Available on Website

Catalog US

Available on Website

**Header**

3D Model

Available on Website