



Actual



Representative

**Catalog Number:** 5359  
**Product ID:** 7TAD012210R0013  
**UPC Number:** 78621005359  
**EAN Number:** 05414363100058  
**Status:** A

3 Inch 90 Degree Malleable Iron Insulated Liquidtight Connector

- Ability to install quickly with low torque effort
- To positively bond conduit to box or enclosure.

### North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Connectors-90 Degree
Application	Used where flexible metal raceway is installed in outdoor or indoor locations where exposed to continuous or intermittent moisture.
Standard	UL E23018, CSA
Size	3 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated/Chromate Coating

### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	3 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Other
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

### Packaging

Outer Quantity	1
Outer Dimensions (inches)	16.6x5.1x8.5
Weight Uom	1286.5 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000122
Catalog Page	Available on Website
Instruction Sheet	TA00210-TB2
Support/Tools	Available on Website
Catalog US	Available on Website

### Header

3D Model	Available on Website
----------	----------------------

