



Actual



Representative

Catalog Number: 5359GR
Product ID: 7TAD012310R0044
UPC Number: 78621089638
Status: A

3 Inch 90 Degree Malleable Iron External Bonding Liquidtight Insulated Connector

- Ability to install quickly with low torque effort

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Grounding Connectors-90 degree
Application	To positively bond conduit to box or enclosure
Standard	UL E3060, CSA
Size	3 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated/Chromate Coating

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	3 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Other
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

Packaging

Outer Quantity	1
Outer Dimensions (inches)	16.12x8.5x4.12
Weight Uom	14.25 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000120
Catalog Page	Available on Website
Support/Tools	Available on Website
Catalog US	Available on Website

Header

3D Model	Available on Website
----------	----------------------