



Actual



Representative

**Catalog Number:** 5365  
**Product ID:** 7TAD012270R0001  
**UPC Number:** 78621005365  
**EAN Number:** 05414363075868  
**Status:** A

1-1/4 Inch Straight Malleable Iron Chase Liquidtight Insulated Connector With Electro-Zinc Plating

#### North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Chase Connectors-Straight
Standard	UL E23018, CSA
Size	1-1/4 Inch
Material	Malleable Iron
Finish	Electro Zinc Plating

#### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 1/4 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Other
Surface protection	Zinc coated
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

#### Packaging

Inner Quantity	5
Inner Dimensions (inches)	8.25x5.25x4.25
Outer Quantity	25
Outer Dimensions (inches)	21x5.5x8.62
Weight Uom	96.5 lbs. per 100

#### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000122
Instruction Sheet	TA00210-TB2

#### Header

3D Model	Available on Website
----------	----------------------