



Actual



Representative

**Catalog Number:** 5369  
**Product ID:** 7TAD012270R0005  
**UPC Number:** 78621005369  
**EAN Number:** 05414363100096  
**Status:** A

3 Inch Straight Malleable Iron Chase Liquidtight Insulated Connector With Electro-Zinc Plating

**North American Specifications (UNSPSC)**

|                  |  |
|------------------|--|
| UNSPSC           | 39121420 Liquid tight connectors                   |
| IGCC             | 4585 Liquid tight connectors                       |
| Type             | Liquidtight Flexible Metal Conduit Fittings        |
| Special Features | UL Listed Liquidtight and CSA Certified Watertight |
| Standard         | CSA, UL E23018                                     |
| Size             | 3 Inch   |
| Material         | Malleable Iron - Insulated                         |

**European Specifications (ETIM)**

|   |  |
|---|--|
| ETIM  | EC001180 Screw connection for protective metallic hose |
| Nominal size in inch                                | 3 inch   |
| Model   | Straight   |
| Revolving thread                                    | N  |
| Construction type                                   | External thread  |
| Connection type screw connection to housing         | Thread   |
| Thread type   | NPT  |
| Thread connection size                              | Other  |
| One-piece   | N  |
| Material housing                                    | Other  |
| Surface protection                                  | Zinc coated  |
| Approved in combination with protective conduit CSA | Y  |
| Approved in combination with protective conduit UL  | Y  |

**Packaging**

|                           |                |
|---------------------------|----------------|
| Inner Quantity            | 1              |
| Outer Quantity            | 5              |
| Outer Dimensions (inches) | 12.8x10.5x4.19 |
| Weight Uom                | 2.8 lbs. Each  |

**Documents / Support Tools**

|                                |             |
|--------------------------------|-------------|
| Technical Drawing / Data Sheet | TDS000122   |
| Instruction Sheet              | TA00210-TB2 |

**Header**

|          |                      |
|----------|----------------------|
| 3D Model | Available on Website |
|----------|----------------------|