



Representative

**Catalog Number:** 5371  
**Product ID:** 7TAD012270R0007  
**UPC Number:** 78621005371  
**EAN Number:** 05414363075882  
**Status:** A

3/8 Inch 90 Degree Malleable Iron Chase Liquidtight Insulated Connector With Electro-Zinc Plating

### North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Liquidtight Flexible Metal Conduit Fittings
Special Features	UL Listed Liquidtight and CSA Certified Watertight
Standard	CSA, UL E23018
Size	3/8 Inch
Material	Malleable Iron - Insulated

### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	3/8 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Other
Surface protection	Zinc coated
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

### Packaging

Inner Quantity	25
Inner Dimensions (inches)	8x5x4
Outer Quantity	50
Outer Dimensions (inches)	8.43x5.18x8.12
Weight Uom	25.5 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000122
Catalog Page	Available on Website
Instruction Sheet	TA00210-TB2

### Header

3D Model	Available on Website
----------	----------------------