



Representative

Catalog Number: 5373
Product ID: 7TAD012270R0010
UPC Number: 78621005373
EAN Number: 05414363075905
Status: Active

3/4 Inch 90 Degree Malleable Iron Chase Liquidtight Insulated Connector With Electro-Zinc Plating

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Brand Name	T&B
Type	Chase Connectors-90 degree
Standard	UL E23018, CSA
Size	3/4 Inch
Material	Malleable Iron
Finish	Electro Zinc Plating

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	3/4 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Other
Surface protection	Zinc coated
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

Packaging

Inner Quantity	10
Inner Dimensions (inches)	6x4x4
Outer Quantity	50
Outer Dimensions (inches)	21.7x5x6.8
Weight Uom	42.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000122
Technical Drawing / Data Sheet Canada	Available on Website

Header

3D Model	Available on Website
----------	----------------------