



Representative

Catalog Number: 5374
Product ID: 7TAD012270R0011
UPC Number: 78621005374
EAN Number: 05414363075912
Status: A

1 Inch 90 Degree Malleable Iron Chase Liquidtight Insulated Connector With Electro-Zinc Plating

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Chase Connectors-90 degree
Standard	UL E23018, CSA
Size	1 Inch
Material	Malleable Iron
Finish	Electro Zinc Plating

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Other
Surface protection	Zinc coated
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

Packaging

Inner Quantity	5
Inner Dimensions (inches)	6.3x3.3x4.9
Outer Quantity	25
Outer Dimensions (inches)	24.2x6.2x3.5
Weight Uom	59.75 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000122
Catalog Page	Available on Website
Instruction Sheet	TA00210-TB2

Header

3D Model	Available on Website
----------	----------------------