



Representative

Catalog Number: 5385
Product ID: 7TAD012470R0006
UPC Number: 78621005385
EAN Number: 05415022457230
Status: A

5 Inch Straight Malleable Iron Insulated Liquidtight Connector

- Ability to install quickly with low torque effort
- Used where flexible metal raceway is installed in outdoor or indoor locations where exposed to continuous or intermittent moisture.
- To positively bond conduit to box or enclosure.

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Liquidtight Flexible Metal Conduit Fittings
Special Features	UL Listed Liquidtight and CSA Certified Watertight
Size	5 Inch
Material	Malleable Iron - Insulated

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	Other
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Other
Approved in combination with protective conduit CSA	N
Approved in combination with protective conduit UL	Y

Packaging

Outer Quantity	1
Outer Dimensions (inches)	9.75x8.87x6.62
Weight Uom	2700 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000122
Instruction Sheet	TA00210-TB2
Support/Tools	Available on Website
Catalog US	Available on Website

Header

3D Model	Available on Website
----------	----------------------

